

1200 V, 20 A Silicon Carbide Schottky Diode

Features


- 4th generation SiC merged PIN Schottky technology
- Zero reverse recovery current
- High-frequency operation
- Temperature-independent switching behavior
- AEC-Q101 qualified and PPAP capable
- Humidity resistant











TO-263-2

Package Types: TO-263-2 PN: E4D20120G

Wolfspeed, Inc. is in the process of rebranding its products and related materials pursuant to the entity name change from Cree, Inc. to Wolfspeed, Inc. During this transition period, products received may be marked with either the Cree name and/or logo or the Wolfspeed name and/or logo.

Applications

- Boost diodes in PFC or DC/DC stages
- Free wheeling diodes in inverter stages
- AC/DC converters
- Automotive and traction power conversion
- PV inverters

Benefits

- Replace bipolar with unipolar rectifiers
- Essentially no switching losses
- Higher efficiency
- Reduction of heat sink requirements
- Parallel devices without thermal runaway
- Ideal for outdoor environments

Maximum Ratings (T_c = 25 °C Unless Otherwise Specified)

Parameter	Symbol	Value	Unit	Test Conditions	Note
Repetitive Peak Reverse Voltage	V_{RRM}	1200	.,		
DC Peak Reverse Voltage	V _R	1200	V		
Continuous Forward Current		56	A	T _c = 25 °C	Fig. 3
	I _F	27		T _c =135 °C	
		20		T _c = 150 °C	
Power Dissipation		250	W	T _c = 25 °C	Fig. 4
	P _{tot}	108		T _c =110 °C	
Repetitive Peak Forward Surge Current	I _{FRM}	83	А	T _C = 25 °C, t _P = 10 ms, Half Sine Pulse	
		47		T _c = 110 °C, t _p = 10 ms, Half Sine Pulse	
Diode dV/dt Ruggedness	dV/dt	250	V/ns	V _R = 0-960 V	
Operating Junction and Storage Temperature	T _J , T _{stg}	-55 to +175	°C		

Electrical Characteristics


Parameter	Symbol	Тур.	Max.	Unit	Test Conditions	Note
Forward Voltage	V _F	1.5	1.8	V	I _F = 20 A, T _J = 25 °C	Fig. 1
		2.2			I _F = 20 A, T _J = 175 °C	
Reverse Current	I _R	35	200	μΑ	V _R = 1200 V, T _J = 25 °C	Fig. 2
		65			V _R = 1200 V, T _J = 175 °C	
Total Capacitive Charge	Q _c	110		nC	$V_R = 800 \text{ V}, I_F = 20 \text{ A}$	Fig. 5
					di/dt = 200 A/μs	
					T _J = 25 °C	
Total Capacitance	С	1474		pF	$V_R = 0 \text{ V}, T_J = 25 \text{ °C}, f = 1 \text{ MHz}$	Fig. 6
		100			V _R = 400 V, T _J = 25 °C, f = 1 MHz	
		76			$V_R = 800 \text{ V}, T_J = 25 \text{ °C}, f = 1 \text{ MHz}$	
Capacitance Stored Energy	E _c	33		μJ	V _R = 800 V	Fig. 7

Note: This is a majority carrier diode, so there is no reverse recovery charge.

Thermal Characteristics

Parameter	Symbol	Тур.	Unit	Note
Thermal Resistance from Junction to Case	$R_{\theta JC}$	0.6	°C/W	Fig. 8

Typical Performance








Figure 2. Reverse Characteristics

Typical Performance





Figure 3. Current Derating



3

Figure 4. Power Derating




Figure 5. Recovery Charge vs. Reverse Voltage




Figure 6. Capacitance vs. Reverse Voltage

Typical Performance




Figure 7. Typical Capacitance Stored Energy






Figure 8. Transient Thermal Impedance

Package Dimensions

Package: TO-263-2



Recommended Solder Pad Layout



Part Number	Package	Marking
E4D20120G	TO-263-2	E4D20120

Revision History

Current Revision Date of Release		Description of Changes		
1	August-2020	Initial Release		
2	October-2020	Updated Wolfspeed branding, package drawing, and solder pad layout (Not Released)		
3	November-2023	Corrected Package Drawing L and L1		

Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, air craft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed.com.

REACh Compliance

REACh substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACh SVHC Declaration. REACh banned substance information (REACh Article 67) is also available upon request.

Contact info:

4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.wolfspeed.com/power

© 2023 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc. PATENT: https://www.wolfspeed.com/legal/patents

The information in this document is subject to change without notice.